



Oil



Heavy Duty

## Heavy-duty nitrile-coated gloves with a cotton liner, for robust all-round hand protection

- **Heightened durability:** Stronger and more flexible than PVC, with three times greater durability than heavy-duty leather alternatives, ActivArmr® Hycron® 27-805 nitrile-coated work gloves meet ANSI/ISEA 105-2024 and EN ABRASION LEVEL 4 standards and are particularly suited to oily and greasy conditions
- **Optimized comfort:** Designed with wearer comfort in mind, ActivArmr® Hycron® 27-805 heavy-duty gloves possess a cotton liner, which enhances their breathability, flexibility and overall user-friendliness
- **Reduced surface defect risks:** ActivArmr® Hycron® 27-805 abrasion-resistant gloves are also silicone-free, making them excellent for applications involving metals or automotive manufacture



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

### Applications


- Handling metal sheets & panels
- Metalworking & assembly operations
- Press injection molding
- Seizing and finishing structural parts
- Fixing, clipping parts and wire harnesses; connecting devices
- Assembly & inspection of components
- Opening furnaces draining pumps valves or lines and crackers BTX process

Key Features

- **Unique nitrile formulation:** Tough, hardy abrasion resistance\*
- **Cotton liner:** For protective gloves that ensure optimal comfort
- **Silicone-free design:** Suitably clean for metal and motor manufacture

\*3x greater durability than standard leather alternatives

Performance Standards & Regulatory Compliance



Specifications

| BRAND   STYLE            | DESCRIPTION                                                                                                                           | SIZE      | LENGTH                         | COATING COLOR | PACKAGE                      |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------|-----------|--------------------------------|---------------|------------------------------|
| ActivArm® Hycron® 27-805 | <b>Finishing:</b> Fully Coated<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> Cotton<br><b>Cuff Style:</b> Safety Cuff | 9, 10, 11 | 256-272 mm/ 10.08-10.71 inches | Blue          | 12 pairs/bag, 12 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306.  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699