

Extra-thick disposable latex gloves, offering durable protection for heavy-duty applications

- **Extra defense:** MICROFLEX® 63-293 latex gloves are 3x thicker than standard disposable latex gloves, ensuring greater resistance against snags and tears
- **Comfortable fit:** These thick latex gloves' soft, elastic formulation delivers comfort and flexibility
- **Added protection:** With an extended cuff, these gloves offer workers enhanced forearm and wrist protection
- **Enhanced grip:** MICROFLEX® 63-293 gloves' textured fingertips enhance grip performance
- **Easy donning:** Donning is made easy thanks to the gloves' double-chlorinated design



***CAUTION:** This product contains natural rubber latex, which may cause allergic reactions

Industries

- Automotive
- Automotive Aftermarket
- Life Sciences
- Healthcare

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Picking and fastening components
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- Body panel repair and replacement
- Tire rotation & changes
- Animal care feeding and cleanup
- Maintaining lab furniture and equipment
- Sample taking and processing
- Raw material sample collection
- Extra protection over the wrist and arm

TECHNICAL DATA SHEET

	Product Information
External Glove Surface	Textured Fingers
Audit Standards	EN ISO 13485:2012
Packaging Overview	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage Instructions	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country Of Origin	Malaysia
Product Segmentation	High Risk
Antistatic	Not Tested

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	295 / 11.6		ASTM D3767,EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151,EN 455-1
Palm Thickness (mm/mils)	0.28/11		ASTM D3767,EN 420
Finger Thickness (mm/mils)	0.36/14.2		ASTM D3767,EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 34	≥ 21	ASTM D412 & D573
Elongation at Break (%)	≥ 850	≥ 750	ASTM D412
Force at break (N)	≥ 15	≥ 10	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	63293070	63293080	63293090	63293100

Performance Standards and Regulatory Compliance

EN ISO 374-1:2016
Type B

EN 374

EN 421

EN ISO 374-5

EN 374

K P T

VIRUS

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01
Asia Pacific Region
MY +603 8310 6688
apac.medical@ansell.com
CN: +86 21 38275000
infochina@ansell.com
JP: +813 5549 8151
info.medical.jp@ansell.com

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445
Latin America & Caribbean Region
BR +55 (11) 3356-3100
latam.medical@ansell.com
MX: +52 442 296 2050
latam.medical@ansell.com
CO: +57 1 288 3247
latam.medical@ansell.com

Australia
Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578
Russia
Ansell PYC
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

