

## Robust, lightweight and durable PU dry diving suit ideal for warm water and climates .

- **Advanced defenses:** The VIKING™ Haztech dry diving suit features a high frequency welded seams that provide additional strength and safety in warm water and climates
- **Increased protection:** This protective diving suit was tested and approved for flex cracking after > 200 flexes down to -40°C
- **Enhanced safety:** In addition, this protective suit has been approved for HZ chemical and BIO micro-organism as it meets the standards for protection against chemicals and infective agents



## Industries

- Emergency Medical Services
- Commercial Diving


## Applications

- Underwater Inspection
- Special Forces Diving
- Underwater Search and Recovery
- Navy Diving
- Inspection Diving
- Flooding applications

## KEY FEATURES & BENEFITS

- ◊ **High frequency welded seams:** Durable dry diving suit
- ◊ **Tested for flex cracking:** > 200 flexes down to -40°C
- ◊ **HZ chemical and BIO approval:** Protects from chemicals, infective agents

## Seam Diagram



## Performance Standards



EN 14225-2:2017 HZ Chemical Resistance

0598

## Product Information

Product Information	
<b>Color</b>	Black, Red
<b>Product Material</b>	TPU (thermoplastic polyurethane), single coated onto a knitted nylon fabric.
<b>Product Reference</b>	HAZTECH
<b>Reinforcements</b>	Black welded reinforcements applied to shoulder area and elbows. Embossed welded knee pads.
<b>Seam Type</b>	Welded and Taped
<b>Available Sizes</b>	S, M, L, XL, 2XL, 3XL
<b>Standards Overview</b>	<ul style="list-style-type: none"><li>• EN 14225-2:2017</li><li>• HZ chemical approval</li><li>• BIO micro-organism approval</li><li>• Tested for flex cracking according to EN ISO 7854</li></ul>

## Suit Components & Accessories

Suit Components and Accessories	
<b>Design Features</b>	Rear entry.
<b>Yoke Options</b>	A full range of helmet yokes is available, such as: SL 27/37, Desco, AH3, Genesis, Gorski, Deepsea and Dräger.
<b>Neck Seal</b>	Fitted with a Surveyor latex neck seal as standard. Option: Bellows latex neck seal; VIKING™ Quick Neck system, which allows for quick changing of broken seals.
<b>Cuffs</b>	Latex PRO cuffs are fitted as standard. Options: Bellows latex cuffs; Conical cuffs. In order to make the suit completely waterproof, it is possible to fit a rubber cuff ring system, alternatively the VIKING™ Bayonet Ring System. Both systems make the fitment of latex gloves or mittens possible.
<b>Footwear And Attachments</b>	Rubber coated 5 mm neoprene boots. The boots feature a non-slip outsole and a heel fin retainer. Option: Nitrile safety boots.
<b>Zipper</b>	Red suits: Medium Duty (MD) magnetic PU zipper; 90 cm long; welded. Black suits: Medium Duty (MD) non-magnetic PU zipper; 90 cm long; welded. The zipper is placed across the shoulders.
<b>Included With Each Delivery</b>	Each suit comes supplied with suspenders, carry bag, user manual, repair kit and zip care materials.

**For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at**

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444

**Australia**  
Ansell Limited  
T: +61 1800 337 041

**Asia Pacific Region**  
Ansell Global Trading Center  
T: +603 8310 6688

**Latin America & Caribbean Region**  
Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending; [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

