

An outstanding combination of cleanliness and safe handling

- A low particle glove with a low level of extractables
- 100% natural rubber, free of pigments or filler
- Ergonomically designed, hand specific gloves provide exceptional dexterity
- Beaded cuff makes donning easier and stays in position on the arm



KEY FEATURES & BENEFITS

Industries

- Controlled and Critical Environments
- Electronics manufacturing

Recommended For

- Clean room cleaning and preparing
- Blending, compounding solids and liquids
- Spill or leakage cleanup
- Transferring liquids and solids
- Loading centrifuges and chromatography columns
- Assembly of parts
- Weighing and dispensing of solid and liquid raw materials



TECHNICAL DATA SHEET


	Product Information
Material	Natural Rubber Latex
Color	Natural
Shape	Hand Specific
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001:2015
Regulatory/Standard Compliance	CE 0493, EN 420:2003 + A1:2009, EN ISO 21420:2020, EN ISO 374-1:2016 Type B, EN ISO 374-1:2016, EN ISO 374-5:2016, EN ISO 374-5:2016, Please consult the IFU, ISO 13485, ISO 14001
Packaging	1 pair per inner poly pack; 25 inner poly packs per master polybag; 8 master polybags of 200 pairs per case/carton
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Available sizes	6.0 (XS), 6.5(S), 7.0 (S), 7.5(M), 8.0(M), 8.5(L), 9.0(L)
Powder Content	Powder-Free
External Glove Surface	Textured Fingers
Internal Glove Surface	Chlorinated
Shelf Life	3 years
Tested for use with Chemotherapy Drugs	No
Protein Level	50 µg/g or less of total extractable protein
Anti-static	No

Physical Properties		Testing Method
Typical Length (mm/in)	300 / 12	EN 420/ASTM D3767
Freedom from Holes	1.5 AQL	EN 455-1/ASTM D3577
Target Single Wall Palm Thickness (mm/mil)	0.21 (+/-0.03) / 8.3	EN 420/ASTM D3767
Target Single Wall Finger Thickness (mm/mil)	0.24 (+/-0.04) / 9.4	EN 420/ASTM D3767
Target Single Wall Cuff Thickness (mm/mil)	0.18 (+/-0.02) / 7.1	EN 420/ASTM D3767
Ultimate tensile strength (MPa) Before Aging	20	ASTM D412-06a
Ultimate tensile strength (MPa) During Aging	NA	ASTM D412-06a

ORDERING INFORMATION

SIZE	6	6.5	7	7.5	8	8.5	9
REORDER NO.	574123	574124	574125	574126	574127	574128	574129

PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.