

# ACTIVARMR™

## 80-658

Heavy duty cut-resistant style with excellent grip and heat protection

Previously known as: Powerflex®80-658



Cut



Heat



Heavy Duty

## High-performance protective gloves, combining cut and heat resistance with excellent grip

- **Advanced defenses:** ActivArm<sup>™</sup> 80-658 safety gloves' steel, fiberglass and aramid liner affords EN ISO E cut resistance, as well as EN 407 level 2 heat contact resistance up to 250°C, for superior hand protection when handling sharp and warm components
- **Specialized protection:** With their latex coating and raised crinkled finish, these sturdy heavy-duty gloves reduce slippage and muscle tension, protecting hands while ensuring strong grip performance
- **Enhanced features:** For added forearm and wrist protection, ActivArm<sup>™</sup> 80-658 industrial gloves feature an extra-long, three quarter-dipped, liquid-repellent cuff, shielding the skin from potentially hazardous liquid solutions
- **Added convenience:** These heather green-colored gloves mask dirt, while remaining washable and available in varying sizes



### Industries

- Construction
- Glass manufacturing
- Automotive
- Recycling and Waste Disposal

### Applications

- Heavy duty handling: where sensitivity is also required
- Handling jagged metal
- Handling of glass sheets, sharp edged objects
- Handling of metal sheets, cutting of dry, painted or galvanised pieces

# ACTIVARMR™

## 80-658


Heavy duty cut-resistant style with excellent grip and heat protection

Previously known as: Powerflex®80-658

### Key Features

- ◆ **Three-layer construction:** Added cut, splinter and burn resistance
- ◆ **Latex coating with crinkled finish:** Firm dry and wet grip
- ◆ **Extra-long cuff:** For work gloves offering forearm and wrist protection

### Performance Standards & Regulatory Compliance



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr™ 80-658	<b>Finishing:</b> Dipped <b>Coating Material:</b> Natural Rubber Latex <b>Liner Material:</b> Stainless steel, Nylon, Fiber glass, Cotton, Aramid <b>Cuff Style:</b> Extra Long	7	6, 7, 8, 9, 10, 11	250-300 mm / 9.84-11.81 inches	Blue	• 12 pairs/bag, 6 bags/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6888  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.