

## Bi-Color Electrical Insulating Gloves Class 3 – RIG316YBBC

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort



Electrical



Light Duty

## Durable, form-fitting electrical safety gloves, offering flexible, comfortable hand protection

- **Heightened flexibility and durability:** ActivArm® Electrical Insulating Gloves Class 3 – RIG316YBBC are made from natural rubber latex (through an eco-conscious dipping process), for electrical safety gloves that are both durable and flexible
- **Advanced ergonomics:** These insulated rubber gloves' non-splayed fingers and hand-at-rest design minimize hand fatigue
- **Elevated comfort:** A spacious flared cuff ensures plentiful room for clothing and ventilation
- **Increased practicality:** A smooth, case-hardened finish makes for easy donning and doffing
- **Certified protection:** As electrical PPE, they also comply with relevant CSA, NFPA and OSHA standards



### Industries

- Automotive
- Electrical
- Construction
- Infrastructure Maintenance
- Machinery and Equipment

### Applications

- Applications with risks that involve heat, cuts and abrasions
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

## Bi-Color Electrical Insulating Gloves Class 3 – RIG316YBBC

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

### Key Features

- **Natural rubber latex formulation:** Flexibility and durability ensured
- **Ergonomic design:** For hand protection with minimal fatigue
- **Generous flared cuff:** Ideal space for clothing and ventilation

### Performance Standards & Regulatory Compliance



In-house testing

EN388: 2016



X243D

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm Bi-Color Electrical Insulating Gloves Class 3 – RIG316YBBC	<b>Coating</b> <b>Material:</b> Natural Latex Rubber <b>Cuff Style:</b> Bell Cuff with rolled beaded edge		9, 9.5, 10, 10.5, 11, 12	410 mm/16inch	Black	1 pair/bag, 10 pairs/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.