

ACTIVARMR™

Electrical Insulating Gloves Class 00 - RIG0011R

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E191



Electrical



Light Duty

Ergonomically designed electrical safety gloves, combining durability and versatile protection*

- **Heightened durability and flexibility:** ActivArmr™ Electrical Insulating Gloves Class 00 - RIG0011R are made from natural rubber latex, for more durable, flexible electrical safety gloves
- **Advanced ergonomics:** These insulated gloves' ergonomic design enables repetitive motion with limited hand fatigue
- **Improved breathability:** Thanks to a generous flared cuff, these low-voltage* electrical gloves offer superb comfort and ventilation
- **Specialized defenses:** Resistant to acid, ozone and very low temperatures**, they are also arc flash certified (APC 1 in combination with 96-002 leather gloves***)
- **Increased practicality:** These electrical protection gloves' case-hardened finish facilitates donning and doffing
- **Certified protection:** They also meet relevant CSA, NFPA and OSHA standards
*Voltage AC maximum 500 V (DC maximum 750)
**Category A, Z and C respectively
***ATPV : 8.9 cal/cm² EBT : 29 with 96-002 leather gloves



Industries

- Automotive
- Construction
- Energy

Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Telecom repair near electrical wires

ACTIVARMR™

Electrical Insulating Gloves Class 00 - RIG0011R


Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E191

Key Features

- ◊ **Natural rubber latex formulation:** For durable, flexible protection
- ◊ **Ergonomic design:** For safety gloves that elicit minimal hand fatigue
- ◊ **Generous flared cuff:** Added room for clothing and ventilation
*Arc flash certified as per IEC 614821-2:2014 and ASTM F2675:2021 standards

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr Electrical Insulating Gloves Class 00 - RIG0011R	Coating Material: Natural Rubber Latex Cuff Style: Straight Cuff with rolled beaded edge	7, 8, 8.5, 9, 9.5, 10, 10.5, 11, Size 12 (subject to MOQ in Australia)	280 / 11	Red	1 pair/pack, 10 pairs/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.