

## Electrical Insulating Gloves Class 2 - RIG214R

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E194



Electrical



Medium Duty

## Flexible, durable high-voltage electrical safety gloves, for dependable hand protection\*

- **Heightened durability and flexibility:** Made from latex through an environmentally conscious dipping process, ActivArm® Electrical Insulating Gloves Class 2 - RIG214R offer durable, flexible electrical protection
- **Advanced ergonomics:** These electrical safety gloves' hand-at-rest shape and non-splayed fingers minimize hand fatigue
- **Elevated comfort:** A flared cuff provides room for clothing and ventilation
- **Increased practicality:** Donning and doffing are made easy thanks to these electrical protection gloves' smooth finish
- **Certified protection:** They are arc flash certified (APC 2 in combination with 96-003 leather gloves), meet relevant NFPA, OSHA and CSA standards, possess EN Category R certification\*, and are Category C cold-resistant
- **Specialized defenses:** They can tolerate a touch voltage AC maximum of 17000 V (DC maximum 25500)  
\*for passing A+Z+H properties (as required by EN standards)



### Industries

- Automotive
- Electrical
- Construction
- Mining
- Machinery and Equipment

### Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

## Electrical Insulating Gloves Class 2 - RIG214R

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E194

### Key Features

- **Natural rubber latex formulation:** For durable, flexible electrical PPE
- **Ergonomic design:** Reduced hand fatigue, increased comfort
- **Generous flared cuff:** Breathability with sufficient room for clothing  
\*Arc flash certified as per IEC 614821-2:2014 and ASTM F2675:2021 standards

### Performance Standards & Regulatory Compliance



### Specifications

| BRAND   STYLE   | DESCRIPTION   | Gauge | SIZE                | LENGTH       | COATING COLOR | PACKAGE                             |
|---|---|-------|---------------------|--------------|---------------|-------------------------------------|
| ActivArm Electrical Insulating Gloves Class 2 - RIG214R | <b>Coating Material:</b><br>Natural Latex Rubber<br><b>Cuff Style:</b> Straight Cuff<br>with rolled beaded edge |       | 8, 9, 10,<br>11, 12 | 360mm/14inch | Red           | • 1 pair/bag,<br>10<br>pairs/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699