

## Electrical Insulating Gloves Class 2 - RIG216Y

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E008



Electrical



Medium Duty

## Sturdy, high-voltage electrical protection gloves offering flexible and comfortable hand protection

- **Heightened durability and flexibility:** ActivArm® Electrical Insulating Gloves Class 2 - RIG216Y are manufactured from natural rubber latex, via an environmentally friendly dipping process, ensuring durable, flexible protection
- **Advanced ergonomics:** These electrical insulated gloves' non-splayed fingers and hand-at-rest form also ensure lesser hand fatigue
- **Elevated comfort:** Thanks to a flared cuff design, these electrical protection gloves ensure ample room for clothing and remain ventilated
- **Specialized defenses:** They can also tolerate a touch voltage of AC $\geq$ 17000 V (DC $\geq$ 25500)
- **Increased practicality:** For easier donning and doffing, they have a smooth, case-hardened finish
- **Certified protection:** They boast EN Category R certification\*, Class 2 arc flash protection\*\* and resist very low temperatures\*\*\*, while also satisfying relevant CSA, NFPA and OSHA standards

\*for passing A+Z+H properties (as required by EN standards)

\*\*in accordance with EN 61482-1-2

\*\*\*Category C



### Industries

- Automotive
- Electrical
- Construction
- Mining
- Machinery and Equipment

### Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

## Electrical Insulating Gloves Class 2 - RIG216Y

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E008

### Key Features

- **Natural rubber latex formulation:** Inherently durable and flexible
- **Ergonomic design:** Greater dexterity and comfort, lesser hand fatigue
- **Generous flared cuff:** Added breathability and room for clothing

### Performance Standards & Regulatory Compliance



In-house testing

EN388: 2016



X232C

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr Electrical Insulating Gloves Class 2 - RIG216Y	<b>Coating Material:</b> Natural Latex Rubber <b>Cuff Style:</b> Straight Cuff with rolled beaded edge		8, 9, 10, 11, 12	410mm/16inch	Yellow	• 1 pair/bag, 10 pairs/carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699