

## FDA approved polymer EPDM+ RABS and Isolator gloves, with dual-colored design

AlphaTec® EPDM Plus RABS and Isolator gloves have a dual-layered breach detection system: unique white material on a black lining; are design from high quality material, in compliance with FDA Food Contact regulations (FDA Positive List) 21 CFR 177 Indirect Food Additives; and are designed for repeated autoclave sterilization (up to 50 times), reducing the need for glove replacements.

### KEY FEATURES & BENEFITS

- **Dual-layered/dual-colored white-on-black design:** Simpler breach detection
- **EPDM Plus composition:** Suited to repeated autoclave sterilization
- **Chemical resistance:** Hydrogen peroxide/common disinfecting chemicals



### TECHNICAL DATA SHEET

|                                           |                                                                                                                                              |
|-------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| Product Reference                         | 85-602                                                                                                                                       |
| Material                                  | Ethylene propylene diene rubber_EPDM plus                                                                                                    |
| Color                                     | White Exterior, Black Interior                                                                                                               |
| Shape                                     | Ambidextrous                                                                                                                                 |
| External Glove Surface                    | Smooth                                                                                                                                       |
| Cuff Style                                | Beaded                                                                                                                                       |
| Storage Instructions                      | Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use.                               |
| Available Sizes                           | 9.5, 11                                                                                                                                      |
| Temperature Range                         | From -20°C to 130°C                                                                                                                          |
| Cleanroom Class                           | Non-Critical Environment                                                                                                                     |
| Shelf Life                                | Three (3) years from date of manufacture.                                                                                                    |
| Tested For Use With<br>Chemotherapy Drugs | No                                                                                                                                           |
| Standards                                 | CE 0493, EN 388:2016 +A1:2018, EN ISO 21420:2020, EN ISO 374-1:2016+A1:2018, EN ISO 374-1:2016 Type B, EN ISO 374-5:2016, Category III, UKCA |

## PHYSICAL PROPERTIES

|                                            | Typical Values | Testing Method |
|--------------------------------------------|----------------|----------------|
| Typical Length (mm/in)                     | 800/32         |                |
| Port Size                                  | 305mm/12"      |                |
|                                            |                |                |
| Target Single Wall Palm Thickness (mm/mil) | 0.51 / 20      |                |
| Target Single Wall Cuff Thickness (mm/mil) | 0.51 / 20      |                |

## PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

| Risk                     | Performance level |
|--------------------------|-------------------|
| Abrasion Resistance      | Level 3           |
| Blade Cut Resistance     | Level 1           |
| Tear Resistance          | Level 0           |
| Puncture Resistance      | Level 0           |
| ISO 13997 Cut Resistance | Level A           |

## ORDERING INFORMATION

|        | PORT SIZE   | 12"/305mm | 12"/305mm |
|--------|-------------|-----------|-----------|
|        | SIZE        | 9.5       | 11        |
| 85-602 | REORDER NO. | 85602095  | 85602110  |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133


#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

## Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.