

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 48-101

Designed for light applications that require good levels of comfort and abrasion resistance

Previously known as: Sensilite<sup>®</sup>



Multi Purpose



Light Duty

## Black PU-coated multi-purpose gloves, designed for comfortable light-duty handling

- **Improved durability:** HyFlex<sup>®</sup> 48-101 industrial gloves boast ANSI- and EN-compliant abrasion resistance, resulting in longer lasting wear
- **Augmented dexterity:** Their thin, flexible nylon liner ensures optimal dexterity, for ease of use in daily applications
- **Black color:** The darker shade of these HyFlex<sup>®</sup> gloves masks dirt, for extended glove life
- **Optimized tactility:** Equipped with thin palm-dipped polyurethane coating, HyFlex<sup>®</sup> 48-101 safety gloves benefit from excellent tactile sensitivity, for precise handling in dry or slightly oily environments
- **Genuine versatility:** Lightweight, durable and tactile, these HyFlex<sup>®</sup> gloves can be used for a variety of different applications



### Industries

- Automotive
- Machinery and Equipment

### Applications

- Chassis assembly, body trimming
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment
- Loading and unloading rough parts or boxes
- Picking parts and accessories

# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 48-101


Designed for light applications that require good levels of comfort and abrasion resistance

Previously known as: Sensilite<sup>®</sup>

### Key Features

- **Palm-dipped PU coating:** ANSI/EN-compliant abrasion resistance
- **Thin nylon liner:** For comfort and dexterity in daily applications
- **Black color:** Dirt-masking PPE gloves, for long-lasting wear

### Performance Standards & Regulatory Compliance



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex <sup>®</sup> 48-101	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> Nylon <b>Cuff Style:</b> Knitwrist	13	6, 7, 8, 9, 10	220-270 mm/ 8.66-10.63 inches	Black	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

