



Nitrile



Neoprene

Chemical-resistant disposable gloves that offer tough chemical protection and unparalleled comfort.

- Three layer design for superior protection against harsh chemicals
- The thinnest chemical resistant disposable glove for enhanced tactility and dexterity
- Extra soft material and ergonomic design for outstanding fit, feel and flexibility
- Lower acceptable pinhole rate (0.65 AQL) for reliable protection against hazardous substances
- Tested against both fentanyl and gastric acid (vomit) to simulate hazardous, real world overdose situations



Industries

- Aerospace
- Automotive
- Automotive Aftermarket
- Life Sciences
- Chemical

Recommended For

- Inspection, selecting, checking parts
- Assembly and inspection of components
- Equipment repair and maintenance
- Production line support and maintenance
- General Purpose Auto Aftermarket
- Oil, fluids and filter change
- Blending, compounding solids and liquids
- Sample taking and processing
- Transferring liquids and solids
- Transferring liquids and solids between vessels and tanks and process equipment



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	93-260
Material	Nitrile + Neoprene (Polychloroprene)
Color	Green
Glove Design	Chlorinated, Powder-Free, Silicone Free, Textured Fingers
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001:2008
Regulatory/Standards Compliance	Category III, EAC TP TC 019:2011, EN ISO 374-1:2016, EN 420:2003 + A1:2009, EN ISO 374-5:2016, EN 374:2003, EN 388:2003, EN 388:2016, EN 421:2010, FDA21 CFR 177-2600, ISO 9001
Packaging	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Sri Lanka
User Needs Segment	High Risk
Available sizes	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11)
Anti-static	Yes

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	285 / 11.2		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	0.65 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.198 / 7.8		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.20 / 7.9		ASTM D3767, EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 22	≥ 26	ASTM D412 & D573
Elongation at Break (%)	≥ 620	≥ 520	ASTM D412
Force at break (N)	≥ 16	≥ 17	EN 455-2

ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Ansell Product Code	93260060	93260070	93260080	93260090	93260100	93260110

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133


Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2020 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.