

## Comfortable nitrile hand protection for a variety of jobs

- **Comfortable fit:** MICROFLEX<sup>®</sup> N85 are a comfortable nitrile gloves with a soft and stretchy feel
- **Secure grip:** Fully textured, they protect while providing a reliable grip
- **Genuine versatility:** Suitable for a wide variety of applications



### Industries

- Automotive
- Automotive Aftermarket
- Food Processing
- Life Sciences

### Recommended For

- Inspection, selecting, checking parts
- Equipment repair and maintenance
- General Purpose Auto Aftermarket
- All food processing, applications that have food contact
- Maintaining lab furniture and equipment
- Assembly of parts
- Sample taking and processing

TECHNICAL DATA SHEET

|                        | Product Information  |
|------------------------|--|
| External Glove Surface | Fully Textured   |
| Audit Standards        | ISO 13485:2003   |
| Packaging Overview     | 100 gloves per dispenser<br>10 dispensers per case<br>1000 gloves per case                               |
| Storage Instructions   | Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition. |
| Country Of Origin      | Malaysia   |
| Product Segmentation   | Multi-Purpose  |
| Antistatic             | Not Tested   |

PHYSICAL PROPERTIES

|   | Typical Values |             | Testing Method      |
|---|----------------|-------------|---------------------|
| Length (mm/inches)                      | 240 / 9.5      |             | ASTM D3767,EN 420   |
| Freedom from Holes (Inspection level I) | 1.5 AQL        |             | ASTM D5151,EN 455-1 |
| Palm Thickness (mm/mils)                | 0.09 / 3.5     |             | ASTM D3767,EN 420   |
| Finger Thickness (mm/mils)              | 0.12 / 4.7     |             | ASTM D3767,EN 420   |
|   | BEFORE AGING   | AFTER AGING |                     |
| Ultimate Tensile Strength (MPa)         | 20             | 16          | ASTM D412 & D573    |
| Elongation at Break (%)                 | ≥ 500          | ≥ 400       | ASTM D412           |

ORDERING INFORMATION

| Size         | XS (5.5 - 6) | S (6.5 - 7) | M (7.5 - 8) | L (8.5 - 9) | XL (9.5 - 10) | XXL (10.5 - 11) |
|--------------|--------------|-------------|-------------|-------------|---------------|-----------------|
| Product Code | N850         | N851        | N852        | N853        | N854          | N855            |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

**Europe, Middle East & Africa Region**  
Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

**Asia Pacific Region**  
MY: +603 8310 6688  
apac.medical@ansell.com  
CN: +86 21 38275000  
infochina@ansell.com  
JP: +813 5549 8151  
info.medical.jp@ansell.com

**North America Region**  
Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

**Latin America & Caribbean Region**  
BR: +55 (11) 3356-3100  
latam.medical@ansell.com  
MX: +52 442 296 2050  
latam.medical@ansell.com  
CO: +57 1 288 3247  
latam.medical@ansell.com

**Australia**  
Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

**Russia**  
Ansell PYC  
Ten. +7 495 258 13 16

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

